

# Rittal – The System.

Faster – better – everywhere.



## SK 3239.800 Blue e+ filter fan

State: 12/06/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3239.800 - Blue e+ filter fan EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 20 – 900 m<sup>3</sup>/h



## Features

|   |   |
|---|---|
| Model No.   | SK 3239.800   |
| Design  | wall-mounted<br>EMC   |
| Product description   | EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3.   |
| Benefits  | Easy filter changes, thanks to a new opening mechanism on the louvred grille<br>Faster installation on the enclosure with optimised detent hooks<br>Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability<br>Tool-free assembly |
| Material  | Plastic   |
| Colour  | RAL 7035  |
| Supply includes   | Complete unit ready to install, including EMC filter mat  |
| Fan   | Axial, shaded pole motor  |
| Air throughput, unimpeded airflow (with chopped-fibre filter) | At 50 Hz: 100 m <sup>3</sup> /h<br>At 60 Hz: 115 m <sup>3</sup> /h  |

# Features

|   |  |
|---|--|
| Air throughput with matching outlet filter including chopped-fibre filter | At 50 Hz: 75 m <sup>3</sup> /h<br>At 60 Hz: 86 m <sup>3</sup> /h   |
| Rated operating voltage   | 230 V, 1~, 50 Hz/60 Hz   |
| Power consumption Pel   | At 50 Hz: 14.7 W<br>At 60 Hz: 16.5 W   |
| Rated current max.  | At 50 Hz: 0.1 A<br>At 60 Hz: 0.12 A  |
| Dimensions  | Width: 204 mm<br>Height: 204 mm<br>Depth: 105 mm   |
| Installation depth  | 84 mm  |
| Mounting cut-out  | Cut-out width: 177 mm<br>Cut-out height: 177 mm  |
| IP protection category to IEC 60529                                       | IP 54 with chopped-fibre filter<br>IP 56 with chopped-fibre filter and hose-proof hood   |
| Protection category NEMA  | Type 12 with chopped-fibre filter<br>Type 3, 3R, 4, 4X with chopped-fibre filter and hose-proof hood                                 |
| Pre-fuse  | Miniature circuit-breaker/fuse: 2 A  |
| Note  | To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays |
| Operating temperature range   | -15 °C...55 °C   |
| Storage temperature range   | -30 °C...70 °C   |
| Noise level   | At 50 Hz: 51 dB(A)<br>At 60 Hz: 54 dB(A)   |
| Packs of  | 1 pc(s).   |
| Net weight  | 1.1 kg   |
| Gross weight  | 1.237 kg   |
| Customs tariff number   | 84145915   |
| ETIM 9  | EC000320   |

# Features

---

|                     |  |
|---------------------|--|
| ETIM 8              | EC000320   |
| ECLASS 8.0          | 27180716   |
| Product description | SK Blue e+ fan-and-filter unit, EMC, 100/115 m <sup>3</sup> /h, 230 V, 1~, 50 Hz/60 Hz, WxHxD 204 x 204 x 105 mm, RAL 7035 |

---

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | CSA<br>30 - KC Korea<br>UL + C-UL - FTTA<br>UR + C-UR (recognized) |
| Explanations | Declaration of conformity  |

---