

**Rittal – The System.**

Faster – better – everywhere.



**SK 3243.066**

**Chopped-fibre filter mat**

State: 17/12/2025 (Source: [rittal.com/uk-en](https://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3243.066 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

Model No.	SK 3243.066
Design	for EMC filter fans
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Copper-nickel-chrome coated chemical fibres
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3243.6.. 3244.6.. 3245.6..
Dimensions	Width: 294 mm Height: 294 mm Depth: 17 mm
Filter class	to DIN EN 779: G3
Packs of	5 pc(s).
Net weight	0.14
Gross weight	0.156
Customs tariff number	56039390
EAN	4028177666252
ETIM 9	EC002513
ETIM 8	EC002513

# Features

---

ECLASS 8.0	27180706
------------	----------

# Approvals

---

Approvals	UR + C-UR (recognized)
Certificates	EAC

---