


Rittal – The System.

Faster – better – everywhere.



SK 3301.380 Vertical shielding

State: 5/09/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3301.380 - Vertical shielding for TS IT

To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.

Features

Model No.	SK 3301.380
Design	Self-adhesive on one side
Product description	To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.
Material	Cellular PU foam Flame-inhibiting to UL 94 (HF1)
Colour	Anthracite
Sealing between	Side panel and 482.6 mm (19") level
Dimensions	Width: 84 mm Height: 1,910 mm Depth: 84 mm
To fit	Width: 600 mm
Packs of	1 pc(s).
Net weight	0.402
Gross weight	0.502
Customs tariff number	39269097
EAN	4028177507975
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261

Tender text

Thin foam rubber, 600 mm rack, vertical LCP shielding

Cellular PU foam, flame-inhibiting to UL 94 (HF1) to block the airflow on the left and right of the 482.6 mm (19 inch) level. For 600 mm wide enclosures.
Length: 1900 mm, self-adhesive

Packs of 1