

Rittal – The System.

Faster – better – everywhere.



SK 3357.100 Guide frame

State: 2/07/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3357.100 - Guide frame for Vario rack-mounted fan

Guide frame for Vario rack-mounted fan: Installation directly in the subrack or using two mounting brackets on the 482.6 mm (19") mounting angles.



Features

Model No.	SK 3357.100
Supply includes	Guide frame Connector and fitted connection cable Mounting bracket for optional attachment to the 482.6 mm (19") mounting level Assembly parts
Length of connection cable	3 m
To fit Model No.	3352.500
Electrical connection	24 V DC 115 - 230 V
Packs of	1 pc(s).
Net weight	1.395 kg
Gross weight	1.52 kg
Customs tariff number	84149000
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK Guide frame, for Vario rack-mounted fan SK 3352.500, for 24 V (DC), 115-230 V