Rittal - The System.

Faster - better - everywhere.





AS 4050.735 Wire end ferrules

State: 12/12/2025 (Source: rittal.com/uk-en)



AS 4050.735 - Wire end ferrules loose

With plastic collar.

Features

AS 4050.735
With plastic collar.
Heat-resistant to 105 °C
E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Grey
10 mm
12
4.8 mm
4 mm²
Yes
UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
AEH DIN 46228
4051.210
Loose
500 pc(s).
0.5
0.5
85369010
4028177805033
EC000005

© Rittal 2025

Features

ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3