

Rittal – The System.

Faster – better – everywhere.



AS 4050.749

Wire end ferrules

State: 14/04/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.749 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4050.749
Design	for wire processing machines
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Black
To fit	Enclosure type: Crimping machine RC Crimping machine R8 Crimping machine R8 E
Length	8 mm
AWG	16
Internal diameter	3.5 mm
For cross-section	1.5 mm ²
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Delivery form	Taped
Packs of	5,000 pc(s).
Net weight	5 kg
Gross weight	0.722 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005

Features

ECLASS 8.0

36659290

Product description

Wire end ferrules According to DIN colour code

Approvals

Approvals

UL + C-UL (listed)
UR