

Rittal – The System.

Faster – better – everywhere.



AS 4051.537 Wire end ferrules

State: 3/08/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.537 - Wire end ferrules on a reel

With plastic collar.

Features

| | |
|--------------------------|---|
| Model No. | AS 4051.537 |
| Product description | With plastic collar. |
| Technical specifications | Heat-resistant to 105 °C |
| Material | E-Cu, galvanic tin-plated Plastic collar: Polypropylene |
| Colour | White |
| Length | 10 mm |
| AWG | 18 |
| Internal diameter | 3.4 mm |
| Rittal colour code | Yes |
| For cross-section | 0.75 mm ² |
| Multinorm | Yes |
| Note | UL-certified in conjunction with the relevant tools, such as crimping machines. |
| Delivery form | Taped |
| Packs of | 4,000 pc(s). |
| Net weight | 4 |
| Gross weight | 0.584 |
| Customs tariff number | 85369010 |
| EAN | 4028177937857 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |

Approvals

Approvals

UL + C-UL (listed)