

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.548 Wire end ferrules

State: 13/05/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.548 - Wire end ferrules on a reel

With plastic collar.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4051.548   |
| Product description      | With plastic collar.  |
| Technical specifications | Heat-resistant to 105 °C  |
| Material                 | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene                      |
| Colour                   | White   |
| Length                   | 8 mm  |
| AWG                      | 20  |
| Internal diameter        | 2.9 mm  |
| For cross-section        | 0.5 mm <sup>2</sup>   |
| DIN colour code          | Yes   |
| Multinorm                | Yes   |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines. |
| Delivery form            | Taped   |
| Packs of                 | 4,000 pc(s).  |
| Net weight               | 4 kg  |
| Gross weight             | 0.46 kg   |
| Customs tariff number    | 85369010  |
| ETIM 9                   | EC000005  |
| ETIM 8                   | EC000005  |
| ECLASS 8.0               | 36659290  |

# Features

---

Product description

Wire end ferrules 0.5 mm<sup>2</sup> x 8 mm AWG 20 multinorm, packs of 4,000 pc(s)., colour: white, delivery form: on belt (in accordance with the DIN colour code), 0.5 mm<sup>2</sup>

# Approvals

---

Approvals

UL + C-UL (listed)