

Rittal – The System.

Faster – better – everywhere.



AS 4051.549 Wire end ferrules

State: 14/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.549 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.549
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Grey
Length	8 mm
AWG	18
Internal diameter	3.4 mm
For cross-section	0.75 mm ²
DIN colour code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Delivery form	Taped
Packs of	4,000 pc(s).
Net weight	4 kg
Gross weight	0.543 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Product description	Wire end ferrules 0.75 mm ² x 8 mm AWG 18 multinorm, packs of 4,000 pc(s)., colour: grey, delivery form: on belt (in accordance with the DIN colour code), 0.75 mm ²
---------------------	--

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------