

Rittal – The System.

Faster – better – everywhere.



AS 4051.574

Wire end ferrules

State: 22/01/2026 (Source: rittal.com/uk-en)

AS 4051.574 - Wire end ferrules loose

With plastic collar.

Features

| | |
|--------------------------|---|
| Model No. | AS 4051.574 |
| Product description | With plastic collar. |
| Technical specifications | Heat-resistant to 105 °C |
| Material | E-Cu, galvanic tin-plated Plastic collar: Polypropylene |
| Colour | Orange |
| Length | 8 mm |
| AWG | 20 |
| Internal diameter | 2.9 mm |
| Rittal colour code | Yes |
| Multinorm | Yes |
| Note | UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant. |
| Delivery form | Loose |
| Packs of | 500 pc(s). |
| Net weight | 0.5 |
| Customs tariff number | 85369010 |
| EAN | 4028177999565 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |

Approvals

Approvals

UL + C-UL (listed)
UR