

**Rittal – The System.**

Faster – better – everywhere.



# AS 4055.481

## Hole punch set, PG

State: 2/07/2026 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.481 - Hole punch set, PG for sheet steel

For punching round cut-outs

## Features

|  |  |
|--|--|
| Model No.  | AS 4055.481  |
| Design   | With 3 cutting points  |
| Product description                                | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.  |
| Supply includes                                    | 5 female dies<br>5 male dies<br>2 tension screws with ball bearing Ø 9.5 x 50 mm<br>HSS pilot drill Ø 11 mm<br>1 tube of lubricant paste<br>Plastic case |
| Machinable material                                | Sheet steel  |
| Maximum machinable material thickness, sheet steel | 2 mm   |
| Ø punch  | 15.2 mm<br>18.6 mm<br>20.4 mm<br>22.5 mm<br>28.3 mm  |
| Note   | When operating with wrenches, tension screws with ball bearings should be used.  |
| Suitable for hydraulic bolt order number           | 4055.661   |
| Packs of   | 1 pc(s).   |
| Net weight   | 0.909 kg   |
| Gross weight                                       | 0.91 kg  |
| Customs tariff number                              | 82051000   |
| ETIM 9   | EC002121   |

# Features

---

|                     |  |
|---------------------|--|
| ETIM 8              | EC002121   |
| ECLASS 8.0          | 21049047   |
| Product description | Sheet metal punches set, PG Ø 15,2/18,6/20,4/22,5/28,3 |

---