Rittal – The System.

Faster – better – everywhere.





AS 4055.537 Splitter hole punch, round

State: 16/11/2025 (Source: rittal.com/uk-en)



AS 4055.537 - Splitter hole punch, round for sheet steel, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.537
Design	With triple splitting
Product description	
Supply includes	Female dies Male dies
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	3 mm
Ø punch	37 mm
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 55 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Net weight	0.281
Gross weight	0.314
Customs tariff number	82073010
EAN	4028177808737
	EC000156

© Rittal 2025

Features

ETIM 8	EC000156	
ECLASS 8.0	21049047	

© Rittal 2025 3