
Rittal – The System.

Faster - better - everywhere.





SZ 4127.010 Door-operated switch

State: 7/11/2025 (Source: rittal.com/uk-en)



SZ 4127.010 - Door-operated switch

with mounting accessories, with or without connection cable.

Features

Model No.	SZ 4127.010	
Design	Without connection cable	
Note	For installation in VX IT only in conjunction with VX mounting bracket for door-operated switch	
Rated impulse withstand voltage, phase to phase	6000 V AC	
Rated insulation voltage	400 V AC	
Installation options	for LED system light for standard and courtesy light without integral door-operated switch for cooling units and air-water heat exchangers	
Electrical connection	240 V AC/6 A 125 V AC/8 A 24 V AC/6 A 24 V DC/6 A	
Rated operating voltage	400 V	
IP protection category to IEC 60 529	IP 40	
Packs of	1 pc(s).	
Net weight	0.068	
Gross weight	0.076	
Customs tariff number	85365019	
EAN	4028177497740	
E-Number Sweden	E3404494	
ETIM 9	EC002626	
ETIM 8	EC002626	

© Rittal 2025

Features

27189266
27189266

Approvals

Approvals	CQC
	CQC-CCC
	CSA
	UL + C-UL (listed)
Explanations	Declaration of conformity
•	Declaration of conformity UK

© Rittal 2025 3