
Rittal – The System.

Faster – better – everywhere.





SZ 4169.000 Punched rail 23 x 23 mm

State: 27/10/2025 (Source: rittal.com/uk-en)



SZ 4169.000 - Punched rail 23 x 23 mm for VX, TS, VX SE

For mounting on the horizontal and vertical enclosure sections via additional assembly components.







Features

Model No.	SZ 4169.000
Material	Sheet steel
Surface finish	Zinc-plated
Length	295 mm
Installation options	In VX on the vertical and horizontal enclosure section using mounting brackets TS In the VX SE, on the vertical enclosure section via mounting brackets in conjunction with the VX adaptor rail In VX SE, on the horizontal extrusion/in the roof via mounting brackets in conjunction with the VX adaptor rail in the depth. On the vertical enclosure section: Directly via support brackets TS, via adaptor rail for PS compatibility in conjunction with angle brackets, mounting brackets or support brackets PS On the horizontal enclosure section: Directly via angle brackets, mounting brackets or support brackets PS
To fit	Enclosure type: VX TS VX SE Suitable for width or height or depth: 400 mm
Packs of	12 pc(s).
Net weight	2.052

© Rittal 2025

Features

Gross weight	2.22
PCF per pack (cradle-to-gate)	8.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177093102
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234

© Rittal 2025 3