

Rittal – The System.

Faster – better – everywhere.



TS 4199.000 Bracket/spacer

State: 22/02/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4199.000 - Bracket/spacer

For flexible attachment of C rails, support rails or cable clamp rails (angle piece). On the sides, to accommodate square sections or tubes (Ø 20 mm). Attachment points with M8 thread.

Features

| | |
|-----------------------|--|
| Model No. | TS 4199.000 |
| Product description | For flexible attachment of C rails, punched rails or cable clamp rails (angle piece). On the sides, to accommodate square sections or tubes (Ø 20 mm). Attachment points with M8 thread. |
| Material | Die-cast zinc |
| Supply includes | 1 pc(s). = 1 bracket/spacer, 2 screws M8 x 16 mm, 2 spring lock washers, 2 cage nuts M8, 2 metal screws |
| Installation options | On the horizontal and vertical VX enclosure section On the punched sections with mounting flanges for the inner mounting level On the vertical TS, VX SE enclosure section via snap-on nuts TS 8800.806 or adaptor rails for VX compatibility On the horizontal TS enclosure section On the horizontal VX SE enclosure section, bottom On the horizontal VX SE enclosure section, top in the depth On enclosures and rails with rectangular system punching 12.5 x 11 mm |
| Note | In VX SE, on the enclosure section in conjunction with VX adaptor rail |
| To fit enclosure type | VX TS VX SE |
| Packs of | 6 pc(s). |
| Net weight | 1.02 kg |
| Gross weight | 1.107 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002625 |

Features

| | |
|---------------------|-------------------|
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | TS Bracket/spacer |
