Rittal – The System.

Faster - better - everywhere.





TS 4199.000 Bracket/spacer

State: 4/11/2025 (Source: rittal.com/uk-en)



TS 4199.000 - Bracket/spacer

For flexible attachment of C rails, support rails or cable clamp rails (angle piece). On the sides, to accommodate square sections or tubes (Ø 20 mm). Attachment points with M8 thread.

Features

Model No.	TS 4199.000	
Product description	For flexible attachment of C rails, punched rails or cable clamp rails (angle piece). On the sides, to accommodate square sections or tubes (Ø 20 mm). Attachment points with M8 thread.	
Material	Die-cast zinc	
Supply includes	1 pc(s). = 1 bracket/spacer, 2 screws M8 x 16 mm, 2 spring lock washers, 2 cage nuts M8, 2 metal screws	
Installation options	On the horizontal and vertical VX enclosure section On the punched sections with mounting flanges for the inner mounting level On the vertical TS, VX SE enclosure section via snap-on nuts TS 8800.806 or adaptor rails for VX compatibility On the horizontal TS enclosure section On the horizontal VX SE enclosure section, bottom On the horizontal VX SE enclosure section, top in the depth On enclosures and rails with rectangular system punching 12.5 x 11 mm	
Note	In VX SE, on the enclosure section in conjunction with VX adaptor rail	
To fit enclosure type	VX TS VX SE	
Packs of	6 pc(s).	
Net weight	1.02	
Gross weight	1.107	
Customs tariff number	73269098	
EAN	4028177093737	

© Rittal 2025

Features

ETIM 9	EC002625	
ETIM 8	EC002625	
ECLASS 8.0	27189234	

© Rittal 2025 3