


Rittal – The System.

Faster – better – everywhere.



VX 5301.254

Side panel, horizontally divided

State: 29/08/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.254 - Side panel, horizontally divided for VX IT

Side panels, horizontally divided, for VX IT

Features

| | |
|-------------------------------------|---|
| Model No. | VX 5301.254 |
| Product description | For sealing IT enclosure systems, both stand-alone and baying arrangements. |
| Benefits | Easy to use Supports tool-free installation and removal of the side wall Locked using security lock 3524 E Integral internal latch |
| Material | Sheet steel |
| Surface finish | Powder-coated |
| Colour | RAL 7035 |
| Supply includes | Console Pedestal 6 mounting brackets 2 lock components Assembly parts |
| To fit | Enclosure type: VX IT Height: = 2,000 mm Depth: = 1,200 mm |
| IP protection category to IEC 60529 | IP 20 |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 21.7 |
| Gross weight | 22.45 |
| PCF per pack (cradle-to-gate) | 85.5 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 94039910 |
| EAN | 4028177950610 |
| E-Number Sweden | E7282563 |
| ETIM 9 | EC002524 |
| ECLASS 8.0 | 27182101 |