Rittal – The System.

Faster – better – everywhere.





VX 5301.326 Levelling feet

State: 10/12/2025 (Source: rittal.com/uk-en)



VX 5301.326 - Levelling feet with internal adjustment, for VX IT

Levelling feet with internal adjustment, to compensate for floor irregularities.



Features

Model No.	VX 5301.326
Product description	The mounting bracket is used to offset and secure the levelling foot beneath the enclosure frame in the interior section. In this way, the levelling foot is conveniently adjusted from the enclosure interior using the multi-tooth drive integrated into the levelling foot shaft.
Supply includes	4 levelling feet, M12, with TX30 hex socket drive 4 mounting brackets Assembly parts
Load capacity	Max. admissible static load: 3000 N per levelling foot
Levelling range	18 - 63 mm
Packs of	4 pc(s).
Net weight	0.76
Gross weight	0.796
Customs tariff number	73269098
EAN	4028177952478
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2025