

# Rittal – The System.

Faster – better – everywhere.



## PC 5368.000

## PC enclosure system

State: 2/02/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PC 5368.000 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | PC 5368.000   |
| Design                              | with glazed door at the top, keyboard drawer and component shelf  |
| Product description                 | Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access. |
| Material                            | Enclosure, door, rear door, mounting compartment, supports: Sheet steel<br>Handles, decorative trim panels: Plastic<br>Door trim panels: Aluminium<br>Viewing window: Single-pane safety glass                                  |
| Surface finish                      | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Mounting compartment, support: powder-coated  |
| Colour                              | Enclosure, door, decorative trim panels, supports: RAL 7035<br>Handle: Similar to RAL 9006<br>Monitor panel, door centre part: RAL 7015   |
| Supply includes                     | Enclosure, door, rear door<br>Glazed door, top<br>Keyboard drawer<br>Component shelf  |
| Dimensions                          | Width: 600 mm<br>Height: 1,600 mm<br>Depth: 836 mm  |
| IP protection category to IEC 60529 | IP 55   |
| Protection category NEMA            | NEMA 12   |

# Features

---

|                                  |                   |
|----------------------------------|-------------------|
| Max. keyboard dimensions (WxHxD) | 480 x 70 x 260 mm |
|----------------------------------|-------------------|

---

|                |             |
|----------------|-------------|
| Basic material | Sheet steel |
|----------------|-------------|

---

|          |          |
|----------|----------|
| Packs of | 1 pc(s). |
|----------|----------|

---

|            |     |
|------------|-----|
| Net weight | 106 |
|------------|-----|

---

|              |     |
|--------------|-----|
| Gross weight | 111 |
|--------------|-----|

---

|     |               |
|-----|---------------|
| EAN | 4028177693197 |
|-----|---------------|

---

|            |          |
|------------|----------|
| ECLASS 8.0 | 27180501 |
|------------|----------|

# Approvals

---

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|

# Tender text

Enclosure system with monitor door and drawer

Enclosure for stand-alone siting, consisting of solid body, glazed door at the top, keyboard drawer, component shelf, bottom door, rear door and welded base assembly. Enclosure body with mounting angles at the front and rear.

System slots on a 25 mm pitch pattern, all round, for individual interior installation and two pairs of mounting angles for space-saving system configuration.

Glazed door top:

With support frame latched from the inside, r/h hinge

- Vertical decorative trim panels
- Pane with screen-printed mask

Component shelf for monitor:

- Slotted, permanently installed

Drawer for keyboard:

- Enclosure
- Keyboard extension piece plus pull-out mousepad
- Front trim panel with handle strip, folded as handrest, with lock no. 3524 E
- With unlatching for glazed door, top

Bottom door:

- Vertical bars with locking rod and double-bit insert,
- hinged on right-hand side,
- door or installation plate folded.

Rear door:

- With locking rod and double-bit insert, hinged on right-hand side
- Gland plates, three-part

Material:

Enclosure, door, gland plates, supports: Sheet steel

- Handles, decorative trim panels: Plastic
- Door trim panels: Aluminium

Surface finish:

- Zinc-plated gland plates

Colour:

- Enclosure, rear door: RAL 7035

Top glazed door:

- Vertical decorative trim panels: RAL 7035

- Pane with screen-printed mask: RAL 7015

Component shelf for monitor: RAL 7015

Drawer for keyboard:

- Enclosure: RAL 7035

- Front trim: RAL 7035/7015/9006

Bottom door:

- Vertical bars: RAL 7035

- Folded installation plate: RAL 7015

External dimensions WHD: 600 x 1600 x 800 mm

Model No.: 5368000

Manufacturer: Rittal GmbH & Co.KG