Rittal – The System.

Faster – better – everywhere.



# DK 5501.310

# Base mount

State: 22/11/2026 (Source: www.rittal.com/uk-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 5501.310 - Base mount for TS IT

To accommodate gland plate modules.

## Features

| | |
|---|---|
| Model No. | DK 5501.310 |
| Product description | To accommodate gland plate modules. |
| Benefits | Tool-free mounting or screw-fastening.<br>Easily retroffitted and combined with stabiliser. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 7035 |
| Supply includes | 2 mounting rails including assembly parts. |
| To fit | Enclosure type: TS IT<br>TX CableNet<br>Depth: 800 mm |
| Packs of | 2 pc(s). |
| Net weight | 1.28 kg |
| Gross weight | 1.6 kg |
| PCF per pack (cradle-to-gate) | 5.7 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Base mount, 2 mounting rails incl. assembly parts, D: 800 mm, for TS IT, TX CableNet, sheet steel, RAL 7035 |

## Tender text

Base mount
For TS IT, TX CableNet
2 mounting rails, incl. assembly parts
Depth: 800 mm
Sheet steel, RAL 7035