

Rittal – The System.

Faster – better – everywhere.



DK 5501.625

**Component shelf 2 U, static
installation**

State: 14/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.625 - Component shelf 2 U, static installation

Component shelf 2 U, static installation for attachment to the 482.6 mm (19") system punchings.
Load capacity: 25 kg.



Features

| | |
|-------------------------------|--|
| Model No. | DK 5501.625 |
| Design | 482.6 mm (19") |
| Product description | For mounting between 482.6 mm (19") mounting angles. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Load capacity | 25 kg surface load, static |
| Note | Not suitable for combination with telescopic slides. |
| Dimensions | Width: 482.6 mm Depth: 400 mm |
| Packs of | 1 pc(s). |
| Net weight | 3.297 kg |
| Gross weight | 3.52 kg |
| PCF per pack (cradle-to-gate) | 11.4 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |

Features

| | |
|-----------------------|--|
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Component shelf, WHD: 482,6x2 Ux400 mm, 25 kg, static, distance between levels:, static installation, For 482.6 mm (19") system punchings, RAL 9005 |