

Rittal – The System.

Faster – better – everywhere.



DK 5501.835

**Air baffle plates for TS IT 482.6 mm
(19") mounting angles**

State: 21/06/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.835 - Air baffle plates for TS IT 482.6 mm (19") mounting angles

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



Features

| | |
|----------------------|--|
| Model No. | DK 5501.835 |
| Product description | With all-round brush strip for collision-free shielding with installed bar systems on the outer mounting level. |
| Applications | To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system. |
| Material | Sheet steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Supply includes | 2 vertical trim panels 2 horizontal trim panels 4 brush strips 4 cellular PU foam pieces Assembly parts 6 blanking panels, 1 U |
| Assembly instruction | The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning. The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles. |

Features

| | |
|-----------------------|---|
| To fit | Width: 800 mm Height: 2,200 mm |
| Packs of | 1 pc(s). |
| Net weight | 8.74 kg |
| Gross weight | 9.2 kg |
| Customs tariff number | 56090000 |
| ETIM 9 | EC000331 |
| ECLASS 8.0 | 27189272 |
| Product description | DK Air baffle plate, WxH: 800x2200 mm, For TS IT 482.6 mm (19") mounting angles |

Tender text

Air baffle plate

Air baffle plate to separate hot/cold zones within an enclosure or complete enclosure suites.

An all-round brush strip ensures collision-free shielding with installed bar systems on the outer mounting level.

Tool-less mounting on the mounting angles of the 482.6 mm (19") level via quick-action fastener or screw-fastened as an option.

May be used, for example for Rittal enclosure series TS IT.

For enclosure (WxH) 800x2000 mm.

Integral mounting holes for optional accommodation of up to 3x1 U components in 482.6 mm (19") width format per side.

Trims pre-configured with 482.6 mm blanking panels, made from plastic, tool-less quick assembly.

Material: Air baffle plates, sheet steel,
Brush strips and 482.6 mm (19") blanking
Plastic UL 94- HB

Model No. DK: 5501.835

Manufacturer: Rittal