

Rittal – The System.

Faster – better – everywhere.



DK 5502.120 Cable route

State: 27/06/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.120 - Cable route for TS

For cable clamping and routing with network and server applications.



Features

Model No.	DK 5502.120
Benefits	Simple assembly with tool-free quick-release fastening Alternatively suitable for screw-fastening Multi-functional punchings for cable management accessories
Applications	For cable clamping and routing with network and server applications
Material	Sheet steel
Colour	RAL 9005
Note	Mounting across the entire depth with 800 mm width, with 600 mm width mounting only behind the second 482.6 mm (19") level
Dimensions	Width: 115 mm
Length	2,000: 2,200 mm
Packs of	1 pc(s).
Net weight	3.6
Gross weight	3.88

Features

Customs tariff number	73269098
EAN	4028177679306
E-Number Sweden	E7239778
ETIM 9	EC000012
ECLASS 8.0	27400703

Tender text

Cable route

For vertical cable routing in network and server enclosures.

The cable route is extendable and can be used for 2000 and 2200 mm high enclosures.

Tool-free mounting between the upper and lower section of the enclosure frame by means of a quick-release fastening.

Alternatively suitable for screw-fastening.

Multi-functional punchings across the entire height of the cable route make individual cable routing and the combined use of different cable routing components possible.

May be used for Rittal enclosure series TS, TS IT.

Material: Sheet steel

Colour: RAL 9005

Model No. DK: 5502.120

Manufacturer: Rittal