

Rittal – The System.

Faster – better – everywhere.



CP 6205.100 Mounting bracket

State: 23/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6205.100 - Mounting bracket for interior installation

For installing punched sections with mounting flanges and support strips, horizontally and vertically. Comfort Panel from an installation depth of 74 mm or Optipanel from an installation depth of 100 mm. In conjunction with the rail for interior installation, the mounting bracket allows the LED system light to be fitted without machining and without the use of tools.



Features

Model No.	CP 6205.100
Product description	For installing punched sections with mounting flanges and support strips, horizontally and vertically. Comfort Panel from an installation depth of 74 mm or Optipanel from an installation depth of 100 mm. In conjunction with the rail for interior installation, the mounting bracket allows the LED system light to be fitted without machining and without the use of tools.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Installation options	Comfort Panel from an installation depth of 74 mm Optipanel from an installation depth of 100 mm Rail for interior installation AX
Assembly instruction	For installation in AX sheet steel, only in conjunction with rail for interior installation AX
Packs of	4 pc(s).
Net weight	0.36 kg
Gross weight	0.4 kg

Features

PCF per pack (cradle-to-gate)	1.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73182900
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	CP Mounting bracket, for interior installation, for Comfort Panel and Optipanel