

Rittal – The System.

Faster – better – everywhere.



CP 6205.100 Mounting bracket

State: 14/05/2024 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6205.100 - Mounting bracket for interior installation

For installing punched sections with mounting flanges and support strips, horizontally and vertically. Comfort Panel from an installation depth of 74 mm or Optipanel from an installation depth of 100 mm. In conjunction with the rail for interior installation, the mounting bracket allows the LED system light to be fitted without machining and without the use of tools.



Features

| | |
|-----------------------|---|
| Model No. | CP 6205.100 |
| Product description | For installing punched sections with mounting flanges and support strips, horizontally and vertically. Comfort Panel from an installation depth of 74 mm or Optipanel from an installation depth of 100 mm. In conjunction with the rail for interior installation, the mounting bracket allows the LED system light to be fitted without machining and without the use of tools. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Installation options | Comfort Panel from an installation depth of 74 mm Optipanel from an installation depth of 100 mm Rail for interior installation AX |
| Assembly instruction | For installation in AX sheet steel, only in conjunction with rail for interior installation AX |
| Packs of | 4 pc(s). |
| Weight/pack | 0.376 kg |
| Customs tariff number | 83024900 |

Features

| | |
|------------|---------------|
| EAN | 4028177536197 |
| ETIM 7.0 | EC002620 |
| ECLASS 8.0 | 27189261 |