

Rittal – The System.

Faster – better – everywhere.



TP 6748.600

One-piece consoles TP

State: 11/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 6748.600 - One-piece consoles TP

One-piece console for operating and monitoring, with large mounting plate and a high protection category of IP 55, available in four different widths. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

Features

| | |
|-----------------------------------|---|
| Model No. | TP 6748.600 |
| Material | Enclosure: Sheet steel 1.5 mm Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Sheet steel, 3.0 mm |
| Surface finish | Enclosure, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated |
| Colour | RAL 7035 |
| Supply includes | Enclosure, solid back and sides Door or double door at front, with locking rod Mounting plate Cover hinged at rear, 2 stays with automatic locking. Automatic unlocking on the left, manual unlocking on the right Gland plates |
| Dimensions | Width: 800 mm Height: 975 mm Depth: 400 mm |
| Dimensions mounting plate (W x H) | 730 mm x 900 mm |
| Depth (top) | 500 mm |
| Depth (bottom) | 400 mm |
| Number of doors | 1 |
| IK Code | IK08 |
| Note | Positioning slide VX 5051.172 can be used as a mounting aid for base/plinth system VX in its new design |

Features

| | |
|-------------------------------------|--|
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Basic material | Sheet steel |
| Dimensions | Width: 800 mm Height: 975 mm Depth (top): 500 mm Depth (bottom): 400 mm |
| Packs of | 1 pc(s). |
| Net weight | 62.5 kg |
| Gross weight | 63.7 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |
| Product description | TP one-piece console, WHD1: 800x975x400/D2: 500 mm, sheet steel |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |