

Rittal – The System.

Faster – better – everywhere.



DK 7072.200 Brush strip

State: 4/04/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7072.200 - Brush strip

Cut-outs for cable routing at any given positions in the side panel, rear panel, doors, roof and gland plate may be finished off attractively by simply attaching the brush strip.

Features

Model No.	DK 7072.200
Product description	For individual installation of enclosure panels, gland plates and panels. Cut-outs for cable routing at any given positions in the side panel, rear panel, doors, roof and base plate may be finished off attractively by simply attaching the brush strip.
Benefits	Snap-on surface: 10 mm
Function principle	Maximum cut-out height: 38 mm
Material	Plastic sheathing: 18 mm Brush strip: Plastic, UL 94-HB
Bristle length	30 mm
Length	2 m
Dimensions	Length: 2 m
For material thicknesses	0.6 - 1.5 mm
Packs of	1 pc(s).
Net weight	0.43 kg
Gross weight	0.433 kg
Customs tariff number	96035000
ETIM 9	EC012298
ECLASS 8.0	27142421
Product description	DK Brush strip, L: 2 m, bristle length: 30 mm, for metal thickness: 0.6-1.5 mm

Tender text

Brush strip

Brush strip, L: 2000 mm,
for sheet thickness: 0.6-1.5 mm

Bristle length: 30 mm

Plastic jacket: 18 mm

Attachable area: 10 mm

Maximum cut-out height: 38 mm