
Rittal - The System.

Faster – better – everywhere.





DK 7119.140


Component shelf 1 U, static installation

State: 7/12/2025 (Source: rittal.com/uk-en)



DK 7119.140 - Component shelf 1 U, static installation 482.6 mm (19") system punchings

482.6 mm (19")/535 mm (metric), support surface for small active components such as modems or mini-hubs in 482.6 mm (19") or metric levels, load capacity: 10 kg.



Features

119.140
mm (19") version
deal support surface for small active components such as ems or mini-hubs.
t steel
7035
surface load, static
uitable for combination with telescopic slides. Installation height inside the U approx. 35 mm
n: 482.6 mm n: 140 mm
s).
g CO2 eq (Cat B)

© Rittal 2025 2

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177221444
ETIM 9	EC002620
ECLASS 8.0	27189261

Tender text

482.6 mm (19 inch) single-level component shelf, D: 140 mm

Load capacity: 10 kg surface load, static

Material: Sheet steel, spray finished in RAL 7035

© Rittal 2025 3