

Rittal – The System.

Faster – better – everywhere.



DK 7493.230 Levelling feet

State: 14/08/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7493.230 - Levelling feet with vibration dampening

Levelling feet with vibration dampening.

Features

Model No.	DK 7493.230
Product description	For vibration insulation of enclosures and to compensate for floor irregularities. The levelling foot is comprised of a disc of reinforced polyamide and an M12 screw, zinc-plated, with ball joint pendulum plus anti-slip and insulating plate for buffering. The insulating plate is resistant to water, mineral oils, petrol, alkaline and acid solutions, salts, soap lye and detergents. Also suitable for special applications such as chemical and laboratory environments.
Max. load capacity (static) per component	300 kg
Dimensions	Thread length: 50 mm
Packs of	4 pc(s).
Net weight	0.52
Gross weight	0.569
Customs tariff number	73181900
EAN	4028177552661
E-Number Sweden	E7239535
ECLASS 8.0	27182003