

# Rittal – The System.

Faster – better – everywhere.



## DK 7826.750

### Vent cover

State: 4/09/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7826.750 - Vent cover for VX, VX IT

For connecting sealed racks to a ventilation system. The stepped connection is suitable for standard pipe diameters 150 mm and 200 mm, thereby ensuring effective cooling due to targeted air exchange inside the rack.



## Features

Model No.	DK 7826.750
Product description	The ideal addition for incorporating sealed racks into an existing central climate control system. The stepped connection is suitable for standard pipe diameters, thereby ensuring effective cooling thanks to targeted air exchange inside the rack.
Material	PET-G
Colour	Transparant
Supply includes	Assembly parts
Ø Hose connection	150 mm 200 mm
Note	Required cut-out in the roof plate (W x D): 380 x 230 mm
Dimensions	Width: 450 mm Height: 144 mm Depth: 300 mm
Packs of	1 pc(s).
Net weight	0.959
Gross weight	0.96
Customs tariff number	39269097

# Features

EAN	4028177572300
ETIM 9	EC000331
ECLASS 8.0	27189272

# Approvals

Certificates	EAC
--------------	-----

# Tender text

## Vent cover

The ideal addition for incorporating sealed racks into an existing central climate control system. The stepped connection is suitable for standard pipe diameters 150 mm and 200 mm. Maximum cut-out on roof plate: 380 x 230 mm.

Material: PET-G, transparent  
Supply includes: Assembly parts  
Dimensions W x H x D: 450 x 144 x 300 mm