

Rittal – The System.

Faster – better – everywhere.



DK 7826.766

Roof plate, vented

State: 21/07/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.766 - Roof plate, vented for TS, TS IT

In exchange for the standard roof, with and without cable entry.



Features

| | |
|-----------------------|--|
| Model No. | DK 7826.766 |
| Design | One-piece without cable entry |
| Product description | In exchange for the standard roof. 72 mm high roof plate, all-round vent slots, clamp strip for cable entry. The two-piece design with cable entry allows convenient retrofitting. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| To fit | Enclosure type: TS TS IT Width: 600 mm Depth: 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 5.47 |
| Gross weight | 5.758 |
| Customs tariff number | 73269098 |
| EAN | 4028177345584 |
| ETIM 9 | EC000744 |
| ECLASS 8.0 | 27182405 |

Tender text

DK-TS vented roof plate, W x D = 600 x 600 mm

Material: Sheet steel, spray finished in RAL 7035

Dimensions (W x H x D): 600 mm x 0 mm x 600 mm