

Rittal – The System.

Faster – better – everywhere.



DK 7826.806

Roof plate, vented

State: 15/06/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.806 - Roof plate, vented for DK-TS, 97 mm high

In exchange for the standard roof.

Features

| | |
|-----------------------|---|
| Model No. | DK 7826.806 |
| Product description | In exchange for the standard roof. Ventilation holes (Ø 5 mm) are incorporated all-round into the 97 mm high roof plate. In conjunction with the vented glazed and sheet steel door, the roof plate coordinates perfectly with the door design. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Note on Model No. | Extended delivery times. |
| To fit | Enclosure type: DK-TS Width: 800 mm Depth: 1,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 15.39 |
| Gross weight | 16.2 |
| Customs tariff number | 72092690 |
| EAN | 4028177234611 |
| ECLASS 8.0 | 27182405 |

Tender text

Roof plate for cable entry, vented
for DK TS 8

75 mm high roof plate with all-round perforated plate
(3 mm diameter) for passive ventilation.

The roof plate has been designed so that it fits the
ventilated glazed and steel sheet doors.

Cable entry sliding angular bracket at the rear.

Rubber section for fixing the cables and cable bunches
to the sliding and fixed brackets.

Active ventilation can be provided by retrofitting a
fan plate to the base.

Material: Sheet steel

Spray finish: RAL 7035

for enclosure dimensions: W: 800 mm D: 1000 mm