

Rittal – The System.

Faster – better – everywhere.



DK 7859.080 PSM Zero-U-Space

State: 4/06/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7859.080 - PSM Zero-U-Space

Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.



Features

| | |
|-------------------------------------|--|
| Model No. | DK 7859.080 |
| Product description | Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks. |
| Material | Aluminium section, natural anodised |
| Length | 1,695 mm |
| Type of electrical connection | Wago jack X-COM |
| Qty. | 2 |
| Phases per infeed | 3~ |
| Rated current (max.) | 16 A |
| Module slots (max.) | 6 |
| IP protection category to IEC 60529 | IP 20 |
| Assembly instruction | Various connection cables, also for single-phase connection |
| Dimensions | Length: 1,695 mm |

Features

| | |
|-----------------------------------|---|
| To fit | Enclosure type: VX IT Height: ≥ 2,000 mm |
| Operating temperature range | 5 °C...45 °C |
| Ambient humidity (non-condensing) | 10...90 % |
| Packs of | 1 pc(s). |
| Net weight | 2.5 kg |
| Gross weight | 2.8 kg |
| Customs tariff number | 85369001 |
| ETIM 9 | EC002762 |
| ECLASS 8.0 | 27371306 |
| Product description | DK modular PDU, PSM busbar, modular power distribution for vertical installation, in the Zero-U-Space for 800 mm wide IT racks, 3~, 16 A, length 1695 mm, module slots: 6, infeeds: 2, connection: WAGO socket, x -COM, for enclosure height 2000 mm, aluminium section, natural anodised |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|