

# Rittal – The System.

Faster – better – everywhere.



## DK 7859.081

## PSM Zero-U-Space

State: 20/02/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))



FRIEDHELM LOH GROUP

# DK 7859.081 - PSM Zero-U-Space

Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.



## Features

Model No.	DK 7859.081
Product description	Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.
Material	Aluminium section, natural anodised
Length	1,695 mm
Length of connection cable	3 m
Type of electrical connection	fixed/CEE
Qty.	1
Phases per infeed	3~
Rated current (max.)	16 A
Module slots (max.)	6
IP protection category to IEC 60 529	IP 20
Dimensions	Length: 1,695 mm

# Features

To fit	Enclosure type: VX IT Height: $\geq$ 2,000 mm
Operating temperature range	5 °C...45 °C
Ambient humidity (non-condensing)	10...90 %
Packs of	1 pc(s).
Net weight	4 kg
Gross weight	4.3 kg
Customs tariff number	85369001
ETIM 9	EC002762
ECLASS 8.0	27371306
Product description	DK modular PDU, PSM busbar, modular power distribution for vertical installation, in the Zero-U-Space for 800 mm wide IT racks, 3~, 16 A, length 1695 mm, module slots: 6, infeeds: 1, connection cable length: 3 m, CEE connector, for enclosure height 2000 mm, aluminium section, natural anodised

# Approvals

Explanations	Declaration of conformity
--------------	---------------------------