

Rittal – The System.

Faster – better – everywhere.



TS 8606.300 TS 8 corner enclosures

State: 11/2015 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

TS 8606.300 - TS 8 corner enclosures

For corner baying of TS 8 enclosures, also with different depths.

Features

Model No.	TS 8606.300
Product description	The corner enclosure and the supplied components will accommodate the various baying options of the TS 8 frame on all outer surfaces. Fitted with a rear panel and an asymmetrical side panel, the corner enclosure also permits the option of baying in both the width and depth. The gland plates are aligned parallel to the rear panel. In TS 8 enclosures with a square footprint, the gland plates may also be rotated through 90°. The baying system is identical to all other TS 8 enclosures.
Material	Sheet steel, 1.5 mm
Surface finish	Enclosure frame, roof, rear wall and side panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame Roof Rear wall (on the longest side) Side panel, asymmetrical Gland plates (divided in a longitudinal direction)
Note on Model No.	Extended delivery times.
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 600 mm
Packs of	1 pc(s).
Net weight	100
Gross weight	104
Customs tariff number	94032080
EAN	4028177251540

Features

ECLASS 8.0

27180101

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity