

# Rittal – The System.

Faster – better – everywhere.



## TS 8610.805 Glazed door

State: 19/07/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8610.805 - Glazed door for TS, TS IT, VX SE

Instead of a sheet steel door or rear panel.



## Features

Model No.	TS 8610.805
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section Corner pieces: Die-cast zinc Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035 Corner pieces: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Viewing door frame with safety glass Locking rod with double-bit insert 180° hinges (4)
Visible area	Viewing window width: 660 mm Viewing window height: 1,840 mm
Viewing window height	1,840 mm

# Features

---

Assembly instruction	Lock components are required when mounting instead of the rear panel
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: TS TS IT VX SE Width: = 800 mm Height: = 2,000 mm
Packs of	1 pc(s).
Net weight	16
Gross weight	17
Customs tariff number	94039910
EAN	4028177693852
ETIM 9	EC000747
ECLASS 8.0	27182204

---