### Rittal - The System.

Faster – better – everywhere.





### TS 8612.520

# TS punched section with mounting flange, 23 x 73 mm

State: 4/11/2025 (Source: rittal.com/uk-en)



## TS 8612.520 - TS punched section with mounting flange, 23 x 73 mm

The alternative to the TS punched section with mounting flange  $17 \times 73$  mm, with punchings for captive nuts/threaded blocks instead of the slotted holes top and bottom. Simply locate and secure.





#### **Features**

Model No.	TS 8612.520
Product description	The alternative to the TS punched section with mounting flange 17 x 73 mm, with punchings for captive nuts/threaded blocks instead of the slotted holes top and bottom. Simply locate and secure.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section
To fit	Enclosure type: the inner mounting level To fit width/depth: 1,200 mm
Packs of	4 pc(s).
Net weight	5.128
Gross weight	5.396
Customs tariff number	73269098
EAN	4028177370555
ETIM 9	EC002625

© Rittal 2025 2

### Features

ECLASS 8.0

27189234

© Rittal 2025 3