



# VX 8617.040

## Punched section with mounting flange, 18 x 64 mm

State: 7/07/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.040 - Punched section with mounting flange, 18 x 64 mm for VX

For variable, individual interior installation of the enclosure frame on the outer mounting level.



## Features

|                      |  |
|----------------------|--|
| Model No.            | VX 8617.040  |
| Product description  | For variable, individual interior installation of the enclosure frame on the outer mounting level.   |
| Benefits             | Simply locate into the system punchings from the outside and screw-fasten<br>System punchings on all four sides<br>With pre-bayed enclosures, the punched sections with mounting flanges may also be fitted from the inside of the enclosure |
| Material             | Sheet steel  |
| Surface finish       | Zinc-plated  |
| Supply includes      | Assembly parts   |
| Installation options | On the outer mounting level, on the enclosure section<br>On the outer mounting level, between two punched sections with mounting flanges 23 x 64 mm  |
| To fit               | Enclosure type: VX<br>Width/depth: 800 mm  |
| Packs of             | 4 pc(s).   |

# Features

---

|                               |   |
|-------------------------------|---|
| Net weight                    | 3.32 kg   |
| Gross weight                  | 3.56 kg   |
| PCF per pack (cradle-to-gate) | 16.66   |
| Customs tariff number         | 73269098  |
| ETIM 9                        | EC002620  |
| ECLASS 8.0                    | 27189234  |
| Product description           | VX Punched section, with mounting flange 18 x 64 mm, for outer mounting level |

# Approvals

---

|              |                 |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|