Rittal – The System.

Faster – better – everywhere.




VX 8618.030

Glazed door

State: 19/11/2026 (Source: www.rittal.com/uk-en)

VX 8618.030 - Glazed door for VX

Instead of a sheet steel door or rear panel.





Features

Model No.	VX 8618.030
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Glazed door Locking rod with double-bit insert 180° hinges (4)
IK Code	IK08
Note	Lock components for frame 8618.110 are required when mounting instead of the rear panel
Type rating to 508A	Type 1 Type 12
IP protection category to IEC 60 529	IP 55
To fit	Enclosure type: VX Width: = 800 mm Height: = 2,000 mm
Packs of	1 pc(s).

© Rittal 2026

Features

Net weight	14.5 kg
Gross weight	15.4 kg
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204
Product description	VX Glazed door, for WH: 800x2000 mm

Approvals

Approvals	UL + C-UL - FTTA
Certificates	Protection category