
Rittal – The System.

Faster – better – everywhere.



# VX 8619.790

# Punched section with mounting flange, 14 x 39 mm

State: 19/11/2026 (Source: www.rittal.com/uk-en)


ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES


FRIEDHELM LOH GROUP

# VX 8619.790 - Punched section with mounting flange, 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.







## Features

| | |
|---|---|
| Model No. | VX 8619.790 |
| Product description | For attaching cable ducts, cable conduit holders, equipment installed on the door, etc. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Distance between fixing points | 635 mm |
| AX installation options | In enclosure height 760 mm, in conjunction with rail for interior installation AX |
| Assembly instruction | For installation in AX sheet steel, only in conjunction with rail for interior installation AX |
| Note | For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required |
| To fit | Enclosure type: AX<br>Suitable for width or height or depth: 760 mm |
| Packs of | 4 pc(s). |

© Rittal 2026

# Features

| | |
|---|---|
| Net weight | 1.2 kg |
| Gross weight | 1.52 kg |
| PCF per pack (cradle-to-gate) | 9.9 |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189234 |
| Product description | VX Punched section with mounting flange, 14 x 39 mm , for door width: 760 mm |

# Approvals

| | |
|---|---|
| Explanations | PCF-declaration |