


Rittal – The System.

Faster – better – everywhere.



TS 8700.060

Side panels, screw-fastened, stainless steel

State: 21/07/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8700.060 - Side panels, screw-fastened, stainless steel for TS

Side panels, screw-fastened, stainless steel, for TS.



Features

Model No.	TS 8700.060
Benefits	Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface
Material	Stainless steel 1.4301 (AISI 304), 1.5 mm
Surface finish	Brushed, grain 400
Supply includes	Assembly parts
To fit	Enclosure type: TS Height: = 2,000 mm Depth: = 600 mm
IP protection category to IEC 60529	IP 55
Basic material	Stainless steel

Features

Packs of	2 pc(s).
Net weight	28.2
Gross weight	29.75
EAN	4028177300170
ECLASS 8.0	27182101

Tender text

Side panel, screw-fastened, stainless steel TS
Screw-fastened side panel, easy positioning on the frame with the location aid.
Automatic potential equalisation and higher EMC protection thanks to enclosure panel fasteners with contact elements.
Protection category IP 55 to IEC60529
Hinged version(optional), max. opening angle 180°.
Material: Stainless steel 1.4301 (AISI 304), 1.5 mm
Surface finish: Brushed, grain 400
for enclosure dimensions: H: 2000 mm D: 600 mm
Side panel, screw-fastened, stainless steel 8700.060