

Rittal – The System.

Faster – better – everywhere.



SV 9346.015 NH slimline fuse-switch disconnecter

State: 16/02/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9346.015 - NH slimline fuse-switch disconnecter with electronic fuse monitoring

Features

Model No.	SV 9346.015
Material	Fibreglass-reinforced polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Colour	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
Supply includes	3 mounting hooks
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M8
Rated operating current max.	160 A
Rated operating voltage	690 V, 3~
For NH size	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 50 mm Height: 400 mm
Connection of round conductors	2.5 - 95 mm ²
To fit busbars	Height: 5, 10 mm
Number of poles	3-pole
Round conductor cross-section	2.5 - 95 mm ²
Packs of	1 pc(s).

Features

Net weight	1.35
Gross weight	1.36
Copper weight (kg per piece)	0.73
Customs tariff number	85369095
EAN	4028177668126
ETIM 9	EC001046
ECLASS 8.0	27371402

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---