


Rittal – The System.

Faster – better – everywhere.



RX 9360.790

RiLineX component adaptor

State: 26/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.790 - RiLineX component adaptor

RiLineX component adaptor (100 A, 3-pole, including connection cables) in width 72 mm for RiLineX and other 60 mm busbar systems. With integral threaded inserts.



Features

Model No.	RX 9360.790
Design	With connection cable
Benefits	For mounting equipment for top hat rail installation, e.g. motor starter Pre-assembled connection cable Simple clip locking for support rails Optional anti-slip guard Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Simple assembly Coordinated accessories reduce the number of different items required
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 2
Rated current (max.)	100 A
Rated current of round conductor	100 A

Features

Rated current of round conductor (UL)	100 A
Electrical ratings UL (SCCR)	100 kA - 600 V, Fuse Class J max. 200 A, JDDZ/7 65 kA - 480 V, circuit breaker max. 70 A, DIVQ/7 50 kA - 480 V, Combination Motor Controller max. 100 A, NKJH/7 30 kA - 600 V, Combination Motor Controller max. 75 A, NKJH/7
Cable outlet	Bottom
For bar systems with centre-to-centre spacing	60 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 72 mm Height: 239.4 mm Depth: 36.6 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Rated impulse withstand voltage U _{imp}	8 kV
Rated insulation voltage U _i	1,000 V
IP protection category to IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C

Features

Ambient humidity (non-condensing)	10...90 %
Packs of	1 pc(s).
Net weight	0.77 kg
Gross weight	0.785 kg
Copper weight (kg per piece)	0.332
PCF per pack (cradle-to-gate)	4.34
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RiLineX component adaptor (100 A, 3-pole, including connection cables) in width 72 mm for RiLineX and other 60 mm busbar systems. With integral threaded inserts.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration

Tender text

RiLineX component adaptor with integral threaded inserts

Device adapters for mounting protective and switching devices for 60 mm busbar systems.

The device is mounted on pre-installed integral threaded inserts.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 100 A

Connection: 35 mm²

Cable outlet: top

Dimensions: 72 mm x 240 mm x 37 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360790