

# Rittal – The System.

Faster – better – everywhere.



## TS 9672.184 Partial doors

State: 2/04/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 9672.184 - Partial doors for TS

Door may be optionally hinged on the right or left.



## Features

Model No.	TS 9672.184
Product description	Suitable for TS enclosures instead of a door or rear panel. The partial doors may be combined with one another as required. A trim panel is required at the top and bottom in each case. Door may be optionally hinged on the right or left. In the case of doors without viewing panel (height 600 – 1000 mm), monitor frame SZ 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type F, and from 600 mm height, for comfort handle.
Material	Sheet steel, 2 mm
Surface finish	Textured paint
Colour	RAL 7035
Supply includes	Cross member Hinges Lock components Assembly parts
Dimensions	Width: 800 mm Height: 400 mm

# Features

To fit	Width: = 800 mm
IP protection category to IEC 60529	IP 54 for a completed enclosure
Packs of	1 pc(s).
Net weight	6.1 kg
Gross weight	7 kg
ETIM 9	EC002525
ECLASS 8.0	27182204
Product description	SV Partial door, WH: 800x400 mm, for TS