

Rittal – The System.

Faster – better – everywhere.



SV 9676.730

Direct connection terminal

State: 21/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.730 - Direct connection terminal for round conductors

For the direct connection of round conductors 95 – 300 mm² (single-wire and multi-wire).

Features

| | |
|--------------------------------|---|
| Model No. | SV 9676.730 |
| Product description | For connecting round conductors to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness. |
| Material | Connection clamp: Brass, tin-plated Busbar claw: Stainless steel |
| Supply includes | Assembly parts (excluding screws) |
| Assembly instruction | The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply. Busbar claw with threaded insert M10 |
| Bars per conductor | 2 |
| Connection of round conductors | 95 - 300 mm ² |
| Mounting dimensions | 60 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.32 kg |
| Gross weight | 0.327 kg |
| Customs tariff number | 85369010 |
| ETIM 9 | EC002270 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Direct connection terminal, round conductor connection 95-300 mm ² , (Flat-PLS 60/100), excluding screw |

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK