


Rittal – The System.

Faster – better – everywhere.



SV 9676.973 Threaded bolts

State: 24/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.973 - Threaded bolts for sliding blocks and sliding nuts

For attaching connection components such as ring terminals.

Features

Model No.	SV 9676.973
Product description	For individual connection options.
Material	Steel
Supply includes	Assembly parts
To fit busbars	Maxi-PLS 45 S/45 Maxi-PLS 60
Dimensions	Thread: M10 Thread length: 55 mm
Packs of	8 pc(s).
Net weight	0.328 kg
Gross weight	0.337 kg
Customs tariff number	73181535
ETIM 9	EC002349
ECLASS 8.0	23110302
Product description	SV Threaded bolt, M10, L: 55 mm

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------