Rittal – The System.

Faster – better – everywhere.





AE 1006.500 Wall-mounted AE

State: 12/11/2025 (Source: rittal.com/us-en)



AE 1006.500 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

Features

Model No.	AE 1006.500
Material	Housing: Stainless steel
	Door: Stainless steel, all-round foamed-in PU seal
	Mounting plate: Carbon steel
	Stainless steel 1.4404 (AISI 316L)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height
	< 0.8 µm
	Mounting panel: Zinc-plated
Supply includes	Housing with door(s)
	Mounting panel
	Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 380 mm
	Height: 380 mm
	Depth: 210 mm
	Width: 15 "
	Height: 15 ″
	Depth: 8.27 "
Dimensions of mounting plate (W	334 mm x 355 mm
x H)	13.1 ″ x 14 ″
Number of doors	1
No. of locks	1

© Rittal 2025

Features

Lock	Lock version: Cam No. of locks: 1
	Lock Insert: 3 mm double-bit
	Material lock: Stainless steel 1.4404 (AISI 316L)
Base material	Stainless steel 1.4404 (AISI 316L)
Packaging unit	1 pc(s).
Net weight	9.31
Gross weight	9.8
Customs tariff number	94032080
EAN	4028177421288
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3