


# Rittal – The System.

Faster – better – everywhere.



## AE 1006.500

### Wall-mounted AE

State: 2/15/2026 (Source: [rittal.com/us-en](https://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1006.500 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

## Features

Model No.	AE 1006.500
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4404 (AISI 316L)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated
Supply includes	Housing with door(s) Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 380 mm Height: 380 mm Depth: 210 mm Width: 15 " Height: 15 " Depth: 8.27 "
Dimensions of mounting plate (W x H)	334 mm x 355 mm 13.1 " x 14 "
Number of doors	1
No. of locks	1

# Features

---

Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit Material lock: Stainless steel 1.4404 (AISI 316L)
Base material	Stainless steel 1.4404 (AISI 316L)
Packaging unit	1 pc(s).
Net weight	9.31
Gross weight	9.8
Customs tariff number	94032080
EAN	4028177421288
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

# Approvals

---

Approvals	DNV-GL UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK