

# Rittal – The System.

Faster – better – everywhere.



## AE 1015.600 Wall-mounted AE

State: 6/21/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1015.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

## Features

Model No.	AE 1015.600
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated
Supply includes	Housing with door(s) Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 400 mm Height: 500 mm Depth: 210 mm Width: 15.7 " Height: 19.7 " Depth: 8.27 "
Dimensions of mounting plate (W x H)	354 mm x 475 mm 13.9 " x 18.7 "
Number of doors	1
No. of locks	2

# Features

---

Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit Material lock: Die-cast zinc, nickel-plated
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	12.65 kg
Gross weight	12.9 kg
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	AE Compact enclosure, WHD: 400x500x210 mm, Stainless steel 1.4301, with mounting plate, single-door, with two cam locks

---

# Approvals

---

Approvals	DNV UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---