

# Rittal – The System.

Faster – better – everywhere.



AE 1017.600

Wall-mounted AE

State: 1/13/2026 (Source: [rittal.com/us-en](https://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1017.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | AE 1017.600   |
| Material                             | Housing: Stainless steel<br>Door: Stainless steel, all-round foamed-in PU seal<br>Mounting plate: Carbon steel<br>Stainless steel 1.4301 (AISI 304) |
| Surface finish                       | Housing and door: Brushed, grain 400, peak-to-valley height<br>< 0.8 µm<br>Mounting panel: Zinc-plated  |
| Supply includes                      | Housing with door(s)<br>Mounting panel<br>Lock: 3 mm double-bit<br>3-point locking system   |
| Protection category NEMA             | NEMA 4X   |
| Protection category IP to EN 60 529  | IP 66   |
| IK code                              | IK08  |
| Dimensions                           | Width: 800 mm<br>Height: 1,200 mm<br>Depth: 300 mm<br>Width: 31.5 "<br>Height: 47.2 "<br>Depth: 11.8 "  |
| Dimensions of mounting plate (W x H) | 740 mm x 1,155 mm<br>29.1 " x 45.5 "  |
| Number of doors                      | 1   |
| Lock                                 | Lock version: 3-point locking system<br>No. of locks: 1<br>Lock Insert: 3 mm double-bit<br>Material lock: Stainless steel 1.4301 (AISI 304)         |

## Features

---

|                       |                                   |
|-----------------------|-----------------------------------|
| Base material         | Stainless steel 1.4301 (AISI 304) |
| Packaging unit        | 1 pc(s).                          |
| Net weight            | 57.8                              |
| Gross weight          | 65.16                             |
| Customs tariff number | 94032080                          |
| EAN                   | 4028177000612                     |
| E-Number Sweden       | E3404426                          |
| ETIM 9                | EC000261                          |
| ETIM 8                | EC000261                          |
| ECLASS 8.0            | 27180101                          |

---

## Approvals

---

|              |   |
|--------------|---|
| Approvals    | DNV-GL<br>Lloyds Register of Shipping<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK   |

---